

# P-164/264 Series Freezeless Wall Hydrant



#### Soft Grip Handle

PRIER P-164 provides a year round source of water in areas that are subject to freezing temperatures. The hydrant valve is connected to the supply piping in the heated portion of the structure, eliminating the possibility of freezing. The P-164 has the added benefit of an easy quarter turn operation that features a proven compression type seal. Additionally, the P-164 features a soft grip operating handle for easy operation in wet conditions and cold weather.

Ordering the P-264 gives you the same style hydrant but with a vandal proof extended lockshield and operating key. It is available from stock in lengths close coupled to 24", longer sizes are available on request.



- **Residential**
- **Freezeless**
- **Anti-Siphon**
- **Backflow Check Valve**

#### **FEATURES**

- Anti-siphon aluminum vacuum breaker with EPDM backflow preventer and backflow check valve
- Quarter-turn soft-grip coated cast aluminum handle
- Wide and enclosed screw holes easily secure mounting screws
- Integral cast flange with built-in drainage pitch
- Solid brass body, valve stem cap, seat and stem ends
- Satin nickel plated body maintains attractive finish
- Stainless steel screws
- Lock shield cap
- AFG teflon with graphite packing for easy maintenance
- Standard "OO" size seat washer
- Each valve air-tested at factory for leak-free quality
- Spout aligning mark with manufacturer's date code

P-164 Length CC- Close Coupled 04- 4" Insertion Operator Inlet 1- Handle Operated D- 1/2" MPT x 1/2" SWT 06- 6" Insertion 2- Vandal Proof Lockshield T- ¾" MPT x ½" FPT 08-8" Insertion C-1/2" CPVC Glue-In 10-10" Insertion S- 1/2" SWT x 3/4" Push-On 12-12" Insertion F- ¾" SWT 14-14" Insertion G-1/2" SharkBite Push-Fit 16-16" Insertion X- 1/2" Crimp PEX 18-18" Insertion W- 1/2" Wirsbo® PEX 20-20" Insertion FX- ¾" Crimp PEX 22-22" Insertion FW- ¾" Wirsbo® PEX 24-24" Insertion Y- 1/2" Press-Fit XX- Special Size

#### **INLET STYLES**

D Style 1/2" MPT x 1/2" SWT



T Style 3/4" MPT x 1/2" FPT

C Style 1/2" CPVC Glue-In



S Style 1/2" SWT x 3/4" Push-On

ORDERING





G Style 1/2" SharkBite Push-Fit

X Style 1/2" Crimp PEX







3/4" Wirsbo® PEX







4515 E. 139th Street Grandview, MO 64030 | (800) 362-9055 | PRIER.com

## P-164/264 REPLACEMENT PARTS

2 - 1 = 2
$\begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ 1 \\ \begin{array}{c} \end{array} \\ \end{array} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} $
A state of the state o

ID	Part No.	Description			
1	See Replacement Stem Section	Stem Assembly, Contains: 1, 4, 10			
2	300-1008	Valve Stem Cap			
3	P-164KT-805	Oval Handle and Screw Kit			
4	C-134KT-802	Seat Washer Replacement Kit (00 Beveled)			
5	C-134KT-803	Stem Packing Replacement Kit			
6	310-1015	Valve Stem Cap for Loose Key			
7	390-1001	Stem Packing Only			
8	C-108KT-808	Oval Style Key on Lanyard			
9	C-144KT-806	Universal Vacuum Breaker Replacement Kit			
10	336-0002	Backflow Check Valve for P-164			
	C-134KT-804	Handle to Loose Key Conversion Kit Contains: 5,6,8			
	P-264KT-804	Loose Key to Handle Conversion Kit Contains: 2, 3, 5			
	P-164KT-807	P-164 Overhaul Kit Contains: 3, 4, 5, 9, 10			

\*The C-144KT-806 Universal Vacuum Breaker Kit fits all current and past PRIER and Mansfield style residential hydrants.

## **REPLACEMENT STEMS**

<i>←</i>	— Stem Overall Length (OAL) — $\rightarrow$

#### H Style Manufactured April 2013 - Present

Part No.	Style	Description	Stem Length
P-231-15CC	Н	Close Coupled Stem for P-164 Hydrant	4 <sup>15</sup> / <sub>32</sub> " OAL
P-231-1504	Н	Stem for 4" P-164 Hydrant	6 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1506	Н	Stem for 6" P-164 Hydrant	8 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1508	Н	Stem for 8" P-164 Hydrant	10 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1510	Н	Stem for 10" P-164 Hydrant	12 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1512	Н	Stem for 12" P-164 Hydrant	14 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1514	Н	Stem for 14" P-164 Hydrant	16 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1516	Н	Stem for 16" P-164 Hydrant	18 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1518	Н	Stem for 18" P-164 Hydrant	20 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1520	Н	Stem for 20" P-164 Hydrant	22 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1522	Н	Stem for 22" P-164 Hydrant	24 <sup>31</sup> / <sub>32</sub> " OAL
P-231-1524	Н	Stem for 24" P-164 Hydrant	26 <sup>31</sup> / <sub>32</sub> " OAL
P-231-15US	н	*Universal Replacement Stem for P-164 Hydrant	Up to 17" OAL

\*\*For stems manufactured before 2013, see P-164 Series retired style spec shet at PRIER.com. PRI-ER universal stems are replacement stems for any size from close coupled to 14." The P-231-15US Universal Stem requires cutting the rod to proper length and soldering the brass stem end to the rod as directed in instructions.

4515 E. 139th Street Grandview, MO 64030 | (800) 362-9055 | PRIER.com